



311 Electrode – 1/8" Dia.
Cronatron Alloy



CW1055

Controlled Hydrogen Coated Electrode for Mild and Low Alloy Steels
85A – 120A (DCRP)

- Pipes and Flanges
- Plates
- Frames
- Channels
- Shafts



333 Electrode – 3/32" Dia.
Cronatron Alloy



CW1049

High Strength for all Weldable Steels and Broken Stud Extraction
60A – 90A (DCRP/AC)

- Broken Bolt Extraction
- Dissimilar Steels
- Leaf Springs
- Tool Steel
- Chain Links



333 Electrode – 1/8" Dia.
Cronatron Alloy



CW1048

High Strength for all Weldable Steels and Broken Stud Extraction
80A – 120A (DCRP/AC)

- Stainless to Carbon Steel
- Broken Bolt Extraction
- Lift Truck Forks
- Gear Teeth
- All-Position



338 Electrode – 1/8" Dia.
Cronatron Alloy



CW1058

Mild Steel, All-Position Alloy for General Welding on Mild Steels
60A – 140A (DCRP/DCSP/AC)

- Galvanized Steel
- Tanks and Tubing
- Sheet Metal
- All-Position



704 Electrode – 1/8" Dia.
Certanium® Alloy



P12657

High Strength, Hydrogen Controlled Alloy for Low/Medium
Carbon Steels and High Strength/Low Alloy Steels
110A – 140A (DCRP/AC)

- High Strength/Low Alloy Steel
- Buckets
- Frames
- Angle Iron
- Machinery



375 Electrode – 1/8" Dia.
Cronatron Alloy



CW1052

High Strength, Hydrogen Controlled Electrode for
High Carbon, Cast Steel and Structural Steel
100A – 130A (DCRP/AC)

- Boilers and Vats
- Structural Steels
- Dozer Blades
- Bucket Teeth
- Cast Steel